

Conversion kit - CF 3000-TOOLKIT 0,25 - 1212376

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Extension kit, complete, for CF 3000, for taped insulated ferrules, 0.25/0.34 mm², sleeve length 8 mm

Why buy this product

- ✔ Suitable for class 2 and class 5 PVC conductors (H05V-K/H07V-K).
Conductors with special insulating material and stranding can only be processed to a limited degree and with reservations.



Key Commercial Data

Packing unit	1 STK
GTIN	 4 046356 461467
GTIN	4046356461467

Technical data

General

Compression	Trapezoidal crimp
Type of contact	Ferrules
Min. AWG, flexible, multi-strand	22
AWG max., flexible, multi-strand	24
Conductor type	PVC
Min. cross section	0.25 mm ²
Max. cross section	0.34 mm ²

Approvals

Approvals

Conversion kit - CF 3000-TOOLKIT 0,25 - 1212376


Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU C- DE.AI30.B.01549
-----	-----------------------------------------------------------------------------------	--------------------------

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>