



Powering Business Worldwide

pe.eaton.com

## Power Supply

### PSG60E24RM

UPC: 786685520971

Dimensions: 55 IN \* 150 IN \* 160 IN (L \* W \* H)

Notes: No Data

**Warranty:** Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

#### Specifications:

- **Special Features:** Varistor transient surge voltage, surge voltage protection against internal surge, safety class 1 with ground connection
- **Enclosure Material:** Metal
- **Output Voltage:** 24 Vdc
- **Series:** PSG
- **Terminals:** Removable
- **Operating Temperature:** -20° to 75°C
- **Wattage:** 60W
- **Phase:** Single-phase

#### Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions Catalog](#)
- [PSG60E24RM AutoCAD 2D Footprint \(mm\) Drawing](#)
- [PSG60E24RM AutoCAD 2D Footprint Drawing](#)
- [PSG60E24RM 2D Drawing Xchange Drawing](#)
- [PSG60E24RM 2D PDF Drawing](#)
- [PSG60E24RM 3D Inventor Drawing](#)
- [PSG60E24RM 3D Model Xchange Drawing](#)
- [Installation Instructions for PSG60E Power Supply Inst Leaflet](#)
- [Eatons PSG Series Power Supplies Product Aid](#)



**Certifications:**

- cUL Certified
- CSA Certified
- cULus/UL 60950-1
- IEC Rated
- UL 508
- EN Listed

**Product compliance:**

- German Safety
- RoHS Compliant
- CE Marked

---

© 2016 Eaton. All rights reserved.