



Main

Device short name	EMA
Provided equipment	Alarm for enable/disable switch
Range of product	SurgeLogic

Complementary

System Voltage	480Y/277 V AC
Device mounting	Flush Surface
Enclosure material	Painted steel
Local signalling	Green normal per phase Red fault per phase
Mounting location	Service entrance
Network number of phases	3 phases
Short-circuit protection	200 kA
Surge current	<= 320 kA per phase
Wiring configuration	3-wire 4-wire

Environment

NEMA degree of protection	NEMA 3R/12
standards	UL 1283 ANSI/IEEE C62.41 ANSI/IEEE C62.45 UL 1449 : ed. 2 UL Category Section 37.3

Offer Sustainability

Not Green Premium product	Not Green Premium product
Will be Compliant on 4Q2016	Will be Compliant on 4Q2016 Will be Compliant on 4Q2016

Contractual warranty

Warranty period	18 months
-----------------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.