

## Main

|                    |                                 |
|--------------------|---------------------------------|
| Device short name  | EMA                             |
| Provided equipment | Alarm for enable/disable switch |
| Range of product   | SurgeLogic                      |

## Complementary

|                          |   |
|--------------------------|---|
| System Voltage           | 600Y/347 V AC                                 |
| Device mounting          | Flush<br>Surface                              |
| Enclosure material       | Painted steel                                 |
| Local signalling         | Green normal per phase<br>Red fault per phase |
| Mounting location        | Service entrance                              |
| Network number of phases | 3 phases                                      |
| Short-circuit protection | 200 kA  |
| Surge current            | <= 320 kA per phase                           |
| Wiring configuration     | 3-wire<br>4-wire                              |

## Environment

|                           |  |
|---------------------------|--|
| NEMA degree of protection | NEMA 3R/12   |
| standards                 | UL 1283<br>ANSI/IEEE C62.41<br>ANSI/IEEE C62.45<br>UL 1449 : ed. 2<br>UL Category Section 37.3 |

## Offer Sustainability

|                           |                           |
|---------------------------|---------------------------|
| Not Green Premium product | Not Green Premium product |
|---------------------------|---------------------------|

## Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|