



2MP Bullet IP Camera

O2B8M

3.3-10mm varifocal motorized lens, dark gray housing



Features

- Supports up to Full HD 1080p @ 30fps
- Motorized lens with auto focus
- Built-in standard PoE (IEEE 802.3af)
- Adaptive IR LEDs reduce IR saturation
- IR Range: 90' (depending on scene reflection)
- True Day/Night operation (IR cut filter)
- 2-way audio communication
- Sensor input and relay output
- Built-in heater and anti-fog glass reduces condensation
- IP66 compliant, weather resistant
- Conformant with ONVIF profile S
- 5 year warranty*



Camera Specifications

| | |
|----------------------|-------------------------------------|
| Image Sensor | Progressive scan 1/2.8" CMOS, 2MP |
| Maximum Resolution | 1920 x 1080 |
| Minimum Illumination | 0 lux (IR LED on) |
| Field of View (H) | 108° - 35° |
| IR Range | 90' (depending on scene reflection) |
| Exposure Control | Yes |
| Digital Slow Shutter | Yes |
| Day/Night | IR cut filter |
| White Balance | Auto, Manual |
| Compensation | BLC / HSBC |
| DNR | Yes |

Video Specifications

| | |
|--------------------|--|
| Main Resolution | 1920x1080 / 1280x720 / 704x480 / 352x240 @ 30fps |
| Compression | H.264, MJPEG |
| Bitrate Control | VBR, CBR |
| Multiple Streaming | 3 streams |

Network Specifications

| | |
|--------------|---|
| Protocols | IPv4, TCP, UDP, RTCP, RTP, RTSP, HTTP, HTTPS, SMTP, FTP, DHCP, Bonjour |
| DDNS support | Speco DDNS (free of charge) |
| Security | User ID & Password protection, IP address filtering, HTTPS |
| User Access | 10 simultaneous users. Performance may vary depending on resolution and number of connections |

Audio Specifications

| | |
|-------------|---------------|
| Mono Input | 64 Kbps G.711 |
| Mono Output | 64 Kbps G.711 |

Client Specifications

| | |
|---------------------|--|
| Web Browser Support | Windows (Internet Explorer 8 and up) |
| PC Application | SecureGuard® VMS |
| Mobile | SecureGuard® Mobile (iPhone® and Android™) |

External Terminal Specifications

| | |
|----------|--------------------------------|
| Ethernet | 10/100 Mbps |
| Alarm | 1 sensor input, 1 relay output |
| Video | BNC out |
| Audio | 1 input, 1 output |
| Power | DC jack |

System Specifications

| | |
|----------------|---|
| PoE | Standard (IEEE 802.3af) |
| Analytics | Motion detection, tampering alarm, trip zone |
| Alarm Triggers | Motion, sensor input, tamper detection, trip zone |
| Alarm Events | FTP video/image file upload, email image upload, micro SD card recording, relay out |
| Video Buffer | Configurable pre-record & post-record |
| Image Settings | Privacy mask |

Operating & Unit Specifications

| | |
|-----------------------|--|
| Power | PoE, 12VDC (power supply not included) |
| Power Consumption | 9W |
| Operating Temperature | -4°F - 122°F |
| Operating Humidity | 8% - 80% RH |
| Unit Dimensions | 3.94" (W) x 3.94" (H) x 8.27" (L) |
| Unit Weight | 3.1 lbs. |
| Certifications | FCC, RoHS |
| Included in Package | Unit, CD (manual, software), mounting screws, L wrench |

Optional Accessories



* Effective on all new purchases as of 2/1/17. ONVIF® is a trademark of Onvif, Inc. Chrome and Firefox use Java which requires an initial internet connection. Apple and the Apple logo are trademarks of Apple Inc., registered in the U.S. and other countries. App Store is a service mark of Apple Inc. Android, Google Play and the Google Play logo are trademarks of Google Inc. Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 9/11/17