



ENGLISH

Datasheet

RS Pro LED 3 AA 500LM High Power Torch

RS Stock No: 901-4985



Sizes:

Torch Overall Length (mm):	155
Diameter (Ø mm):	Head - Ø 41.5, Barrel – Ø 37.5
Batteries Inserted:	3 X AA
Batteries Supply:	Included
Weight (gm), Torch Only:	206



ENGLISH

Features:

Depressing Barrel Switch

Switching Modes – High ON/Low ON /OFF

Functioned by 3 X AA Batteries

Carrying Holster Included

Built-in Multi Option Battery Holder in Use – 3 X AA, 2 X AA or 1 X AA

Lumen Output (ANSI FL1 STANDARD):

3 X AA – 500 LM at High, 150 LM at Low

2 X AA – 280 LM at High, 95 LM at Low

1 X AA – 120 LM at High, 40 LM at Low

Battery Run Time (100% to 10%, ANSI FL1 STANDARD):

3 X AA – 9 Hrs at High, 27 Hrs at Low

2 X AA – 6.5 Hrs at High, 19.5 Hrs at Low

1 X AA – 4.5 Hrs at High, 13.5 Hrs at Low

Battery Power Indicator: On Grip, the indicator turned from GREEN to RED when power is less than 20%

Water Resistant: IPX6

Drop Impact Test: 1 Metre

Materials/Parts

Case: 6463 Aluminium Alloy

Lens: PC

LED: CREE X-PL V4

Package: Folded PVC Blister with RS Card Inserted