

# HG 2520 E

**NEW!**

Available October 2016

## Technical Specifications

Voltage:	120 VAC / 60Hz
Output:	1750 watts
Amps:	14.6
Temperature:	120 – 1300 °F (50 – 700 °C) (continuously variable)
Airflow rate:	2 – 13 cfm. (continuously variable)
Air pressure:	3,000 Pa
Highlights:	Restart protection, LCD display, 4 settings programmable, locable override funktion (LOC), single-hand operation by toggle, magnesium guard sleeve, plug-in heating element, residual heat indicator, construction use, easily replaceable power cord, ergonomic soft grip handle, optional temperature scanner
Power cord:	Industrial grade rubber
Motor:	Brushless motor
Heating element:	Ceramic heating element
Motor lifetime:	Approx. 10,000 hrs.
Heater lifetime:	Approx. 800 hrs.
Accessories:	Use of our professional accessories
Dimensions:	11.20" x 3.80" x 8.20" (l x w x h)
Net Weight:	1.85 lbs (29.63 oz)
Single Sell Pack:	Dimensions: 15.35" x 4.33" x 12.6" Weight: 5.15 lbs (82.44 oz)
Country of origin:	Romania
Warranty:	One year limited



UPC-Code	Prod. No.
018139375906	110025599

