Fuse plug - P-FU 5X20 LED 24 820KOHM - 3036825

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)

Fuse plug, Nominal current: 6.3 A, Fuse type: G / 5 x 20, Fuse type: Glass / ceramics / ..., Color: black

RoHS

Key Commercial Data

Packing unit	1 STK
Minimum order quantity	10 STK
GTIN	4 055626 293639
GTIN	4055626293639
Weight per Piece (excluding packing)	4.000 g
Custom tariff number	85369095
Country of origin	Poland

Technical data

General

Note	Prior to replacing the cartridge fuse, disconnect the fuse connector from the basic terminal block.
Number of levels	1
Color	black
Insulating material	PA
Flammability rating according to UL 94	V0
Fuse	G / 5 x 20
Fuse type	Glass / ceramics / ...
Degree of pollution	3
Maximum power dissipation	1.6 W (Short-circuit and overload protection)

Fuse plug - P-FU 5X20 LED 24 820KOHM - 3036825

Technical data

General

LED voltage range	12 V DC ... 30 V DC
LED current range	0.31 mA ... 0.95 mA
Maximum load current	6.3 A (the current is determined by the fuse used)
Nominal current I_N	6.3 A (the current is determined by the fuse used)
Open side panel	No
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Static insulating material application in cold	-60 °C
Behavior in fire for rail vehicles (DIN 5510-2)	Test passed
Flame test method (DIN EN 60695-11-10)	V0
Oxygen index (DIN EN ISO 4589-2)	>32 %
NF F16-101, NF F10-102 Class I	2
NF F16-101, NF F10-102 Class F	2
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed
Calorimetric heat release NFPA 130 (ASTM E 1354)	28 MJ/kg
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3

Standards and Regulations

Flammability rating according to UL 94	V0

Drawings

Circuit diagram

Classifications

eCl@ss

eCl@ss 4.0	27141199
eCl@ss 4.1	27141199
eCl@ss 5.0	27141145
eCl@ss 5.1	27141145

Fuse plug - P-FU 5X20 LED 24 820KOHM - 3036825

Classifications

eCl@ss

eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27141149
eCl@ss 9.0	27141149

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC000899
ETIM 5.0	EC002018
ETIM 6.0	EC002018

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

Phoenix Contact 2017 © - all rights reserved
http://www.phoenixcontact.com