

End cover - D-UT 2,5/10 OG - 3047219


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



End cover, Length: 47 mm, Width: 2.2 mm, Height: 39.8 mm, Color: orange



Key Commercial Data

| | |
|--------------------------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit | 1 STK |
| Minimum order quantity | 50 STK |
| GTIN |  4 017918 977269 |
| GTIN | 4017918977269 |
| Weight per Piece (excluding packing) | 2.490 g |
| Custom tariff number | 85389099 |
| Country of origin | Germany |

Technical data

General

| | |
|----------------------------------------|--------|
| Color | orange |
| Material | PA |
| Flammability rating according to UL 94 | V0 |

Dimensions

| | |
|--------|---------|
| Width | 2.2 mm |
| Length | 47 mm |
| Height | 39.8 mm |

Standards and Regulations

| | |
|----------------------------------------|----|
| Flammability rating according to UL 94 | V0 |
|----------------------------------------|----|

End cover - D-UT 2,5/10 OG - 3047219

Technical data

Environmental Product Compliance

| | |
|------------|---------------------------------------------------------|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
| | No hazardous substances above threshold values |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27141199 |
| eCl@ss 4.1 | 27141199 |
| eCl@ss 5.0 | 27141145 |
| eCl@ss 5.1 | 27141145 |
| eCl@ss 6.0 | 27141133 |
| eCl@ss 7.0 | 27141133 |
| eCl@ss 8.0 | 27141133 |
| eCl@ss 9.0 | 27141133 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000886 |
| ETIM 3.0 | EC000886 |
| ETIM 4.0 | EC000886 |
| ETIM 5.0 | EC000886 |
| ETIM 6.0 | EC000886 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211827 |
| UNSPSC 7.0901 | 39121424 |
| UNSPSC 11 | 39121424 |
| UNSPSC 12.01 | 39121424 |
| UNSPSC 13.2 | 39121425 |