

## Fixed bridge - FB 2-25 - 3048205

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Fixed bridge, Number of positions: 2, Color: silver

The figure shows the Ex version with additional spring washer

RoHS

### Key Commercial Data

|                                      |   |
|--------------------------------------|---|
| Packing unit                         | 1 STK   |
| Minimum order quantity               | 10 STK  |
| GTIN                                 | <br>4 017918 987350 |
| GTIN                                 | 4017918987350   |
| Weight per Piece (excluding packing) | 76.000 g  |
| Custom tariff number                 | 85389099  |
| Country of origin                    | Germany   |

### Technical data

#### Technical data

|                     |        |
|---------------------|--------|
| Color               | silver |
| Number of positions | 2      |

### Environmental Product Compliance

|            |   |
|------------|---|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
|            | No hazardous substances above threshold values          |

## Fixed bridge - FB 2-25 - 3048205

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27141199 |
| eCl@ss 4.1 | 27141199 |
| eCl@ss 5.0 | 27141140 |
| eCl@ss 5.1 | 27141140 |
| eCl@ss 6.0 | 27141140 |
| eCl@ss 7.0 | 27141140 |
| eCl@ss 8.0 | 27141140 |
| eCl@ss 9.0 | 27141140 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000489 |
| ETIM 3.0 | EC000489 |
| ETIM 4.0 | EC000489 |
| ETIM 5.0 | EC000489 |
| ETIM 6.0 | EC000489 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211829 |
| UNSPSC 7.0901 | 39121426 |
| UNSPSC 11     | 39121426 |
| UNSPSC 12.01  | 39121426 |
| UNSPSC 13.2   | 39121426 |