

Interruption plug - FIP-3/2 SERVICE - 3069920

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Interruption plug, Number of positions: 2, Width: 16.3 mm, Color: red



RoHS

Key Commercial Data

Packing unit	1 STK
GTIN	 4 055626 136875
GTIN	4055626136875
Weight per Piece (excluding packing)	40.000 g
Custom tariff number	85366990
Country of origin	Poland

Technical data

General

Number of positions	2
Color	red
Insulating material	PA
Flammability rating according to UL 94	V0
Rated surge voltage	5 kV
Overvoltage category	III
Insulating material group	I
Open side panel	Yes

Dimensions

Width	16.3 mm
Length	53.4 mm

Interruption plug - FIP-3/2 SERVICE - 3069920

Technical data

Dimensions

Pitch	8.2 mm
-------	--------

Assembly

Mounting type	Insertion in base strip
---------------	-------------------------

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Drawings

Circuit diagram



Classifications

eCl@ss

eCl@ss 5.1	27141120
eCl@ss 6.0	27141141
eCl@ss 8.0	27141190
eCl@ss 9.0	27141190

ETIM

ETIM 4.0	EC000897
ETIM 5.0	EC002848
ETIM 6.0	EC002848

UNSPSC

UNSPSC 13.2	39121410
-------------	----------