

## Spacer - DP-UK 10,3-HESI - 3211238

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Spacer, Color: white



### Key Commercial Data

Packing unit	1 STK
Minimum order quantity	100 STK
GTIN	 4 046356 735841
GTIN	4046356735841
Weight per Piece (excluding packing)	0.200 g
Custom tariff number	39269097
Country of origin	Germany

### Technical data

#### General

Color	white
Material	PA
Flammability rating according to UL 94	V0

#### Standards and Regulations

Flammability rating according to UL 94	V0
--	----

#### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Spacer - DP-UK 10,3-HESI - 3211238

### Classifications

#### eCl@ss

eCl@ss 4.0	27141199
eCl@ss 4.1	27141199
eCl@ss 5.0	27141145
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27141190
eCl@ss 9.0	27141190

#### ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC000886
ETIM 5.0	EC002848
ETIM 6.0	EC002848

#### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410