



NFO-4601



NFO-4602



NFO-4503



NFO-4512



NFO-4720

Wall Mount Fiber Optic Cabinets

- Single door, fiber optic wall mount cabinet
- Available in 1, 2 and 4 strip modules
- 1 strip modules for a maximum capacity of 24 fibers
- 2 strip modules for a maximum capacity of 48 fibers
- 4 strip modules for a maximum capacity of 96 fibers
- Door locking feature
- Cold rolled steel with black powder coat finish



Item #	Color	Description
NFO-4601	BLACK	FIBER OPTIC WALL MOUNT CABINET, 1 STRIP
NFO-4602	BLACK	FIBER OPTIC WALL MOUNT CABINET, 2 STRIPS
NFO-4604	BLACK	FIBER OPTIC WALL MOUNT CABINET, 4 STRIPS

Rack Mount Fiber Enclosures

- Single door, fiber optic rack mount enclosure
- 19" mounting format
- 1U, 3 strip modules for a maximum capacity of 72 fibers
- 2U, 6 strip modules for a maximum capacity of 144 fibers
- 3U, 9 strip modules for a maximum capacity of 216 fibers
- 4U, 12 strip modules for a maximum capacity of 288 fibers
- Cold rolled steel with black powder coat finish



Item #	Color	Description
NFO-4503	BLACK	1U FIBER OPTIC RACK MOUNT PANEL, 3 STRIPS
NFO-4506	BLACK	2U FIBER OPTIC RACK MOUNT PANEL, 6 STRIPS
NFO-4509	BLACK	3U FIBER OPTIC RACK MOUNT PANEL, 9 STRIPS
NFO-4512	BLACK	4U FIBER OPTIC RACK MOUNT PANEL, 12 STRIPS

Splice Trays

- Stackable plastic splice tray
- Available in 6, 12 and 24 position trays
- Use with Rack Mount Fiber Enclosures



Item #	Color	Description
NFO-4720	BLACK	6 POSITION STACKABLE PLASTIC SPLICE TRAY
NFO-4721	BLACK	12 POSITION STACKABLE PLASTIC SPLICE TRAY
NFO-4722	BLACK	24 POSITION STACKABLE PLASTIC SPLICE TRAY