# Plunger Style Test Clips 4mm System





Type

## **KLEPS 250**

Touch proof plunger style test probe with rotating pincers and flexible shaft, allows to clamp wires up to 4mm, 4mm brass socket, fits MLN and MLB leads.

Clamping range Clamp type

PART NO. / Housing color

4 mm (0.157") rotating pincers

973528100

973528101



## **KLEPS 2600**

Safety plunger style test probe with rotating pincers and flexible shaft, allows to clamp wires up to 4mm, 4mm brass socket.

4 mm (0.157") rotating pincers

972306100 **●** 972306101 **●** 

# **Technical Data**

Connection Type Voltage Rating

Measurement Category (IEC61010) Current Rating\* Contact Resistance

#### **Material Specifications**

Pincers/ hook Connection pin/ socket

Contact Spring Housing

# **Environmental Conditions**

Temperature Range Flamability Rating

Housing

socket Ø 4 mm

30 VAC / 60 VDC

CAT I 4 A

100 mOhm

nickel plated spring steel nickel plated brass

\_

PF

# -25 °C to +80 °C (13°F to 176°F)

UL 94 V-0

socket Ø 4 mm AC/DC 1000 V CAT III 4 A 50 mOhm

nickel plated spring steel nickel plated brass


-PBT

-25 °C to +80 °C (13°F to 176°F)

UL 94 HB

#### **Drawing**

Measurements are shown in millimeters. Multiply by 0.03937 to convert to inches.



Handle Handle

<sup>\*</sup> Please consider derating graph on page 80.