Test Plugs 2 mm System







MST 201 Type

> 2mm mini connector pin for PCB boards, fits MKU1 and MBU2 (for stacking PCB boards),

pin spacing 5mm and up.

2 mm (0.078") Pin diameter PART NO. / Housing color 931338001

MST 3

2mm mini connector, nickel plated brass pin with solder connection, flexible and shatter proof insulated sleeve, connecting leads up to 1.9mm.

2 mm (0.078")

973509100

973509101

973509102

973509103 973509104

973509106

Technical Data

Contact Type pin

Connection Type solder terminal 30 VAC / 60 VDC Voltage Rating

Measurement Category (IEC61010) CAT I Current Rating* 6A Contact Resistance 6 mOhm

Material Specifications

Plug nickel plated brass

Contact Spring Housing

Environmental Conditions

-20 °C to +60 °C (-4 to 140°F) Temperature range

Flamability Rating

Housing

spring loaded pin solder terminal 30 VAC / 60 VDC

CAT I 6A 6 mOhm


nickel plated brass


PVC-P

-20 °C to +60 °C (-4 to 140°F)

Drawing

Measurements are shown in millimeters. Multiply by 0.03937 to convert to inches.





^{*} Please consider derating graph on page 80.