Test Plugs


ADD AL PATHONE AND ALL AND AL	2 mi	n System
	MZS 2	CE MST S WS 30 AU
	Shrouded Adapter 2mm plug to 4mm jack.	2mm safety plug, spring loaded pin, gold plated, solder terminal 0.5mm2-1.0mm2, 1000V system.
Pin diameter PART NO. / Housing color	2 mm (0.078") ● 973600100 ● 973600101	2 mm (0.078") 975090700 975090701 975090702 975090703 975090704 975090705 975090706 975090707 975090709
Technical Data Contact Type Connection Type Voltage Rating Measurement Category (IEC61010) Current Rating* Contact Resistance Material Specifications Plug Contact Spring Housing Environmental Conditions	stationary jack Ø4mm 30 VAC / 60 VDC CAT I 6A 6 mOhm nickel plated brass – PP	spring loaded pin solder terminal AC/DC 1000V CAT III 10A 2 mOhm gold plated copper-beryllium gold plated brass Polyamide
Temperature range Flamability Rating Housing	-20 °C to +60 °C (-4 to 140°F) UL94 HB	-15°C to +70°C (-5 to 158°F) -


-

Drawing

Measurements are shown in millimeters. Multiply by 0.03937 to convert to inches.

16





 * Please consider derating graph on page 80.