## **Test Jacks** 2 mm System





MPB 1 Type

2mm mini test jack, dimensions according to DIN41649. Suitable for testing PCB boards

during operation.

2 mm Pin Diameter

930224100 930224101



## MPK 1

2mm insulated panel mount binding post with cross hole, gold plated Copper-Beryllium contact spring, tin plated brass thread bold with solder terminal. max. panel thickness 8mm

2 mm

930268100

930268101

**Technical Data** 

PART NO. / Housing color

spring-loaded jack Ø 2 mm Contact Type

Connection Type solder terminal 30 VAC / 60 VDC Voltage Rating

CAT I Measurement Category (IEC61010) 6 A Current Rating\* Contact Resistance 6 mOhm PCB Mounting Type

**Material Specifications** 

Jack Body

tin plated bronze Contact Spring

PC Housing

**Environmental Conditions** 

-20°C to +60 °C (-4 to 140°F) Temperature Range

Flamability Rating

UL 94 HB Housing

spring-loaded jack Ø 2 mm, cross hole Ø 2 mm

solder terminal 30 VAC / 60 VDC

CAT I 6 A 6 mOhm screw thread M3

gold plated copper-beryllium


Polyamide


-20°C to +60 °C (-4 to 140°F)

UL 94 V-2

## Drawing

Measurements are shown in millimeters. Multiply by 0.03937 to convert to inches.





<sup>\*</sup> Please consider derating graph on page 80.