



Actual

Catalog Number: LT43D-NEW
Product ID: 7TAD012880R0001
UPC Number: 03448108787
Status: Active

1/2 Inch Liquidtight Non-metallic Fitting

- Non-conductive and non-corrosive.
- Resistant to oil, acid, ozone and alkaline.
- Easy to install.
- Approved for indoor and outdoor locations
- UL listed for wet locations
- Nitrile rubber 'O' ring for a liquidtight termination.
- Temperatures up to 225 degree F (107 degree C)
- Meets UL standard 514B.

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Brand Name	Carlon
Type	Liquidtight Fittings
Application	For use with Carflex conduit and Carflex X-Flex conduit.
Standard	cULus
Size	1/2 Inch
Material	Non-Metallic

European Specifications (ETIM)

ETIM	EC001178 Screw connection for protective plastic hose
Nominal size in inch	1/2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Type of connection	Thread
Thread connection size	Other
Thread length	14.22mm
One-piece	N
Material screw gland	Other
Colour	Grey

Packaging

Outer Quantity	50
Outer Dimensions (inches)	11.5x7.7x5.5
Weight Uom	8 lbs. per 100

Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-ac04398

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321

