



Representative

Catalog Number: C 755 6
Product ID: 7TAA004830R0011
UPC Number: 78599103926
Status: Active

Clamp, Cable Insulator, Hole Diameter 2-3/4 Inch, Height 5-1/4 Inches, Width 4-3/4, White-Glaze Porcelain

- Dry process white glaze porcelain insulators assembled in pairs to accept cables from 3/8 Inch thru 4 1/2 Inch O.D.
- C-105 clamp with bronze slotted hex head screw and nut furnished. Fits all Kindorf® channels.

North American Specifications (UNSPSC)

UNSPSC	39121705 Cable clamp and staple
IGCC	5049 Cable clamp and staple
Brand Name	Kindorf
Type	Porcelain Insulator Clamps & Saddles
Special Features	Dry process white glaze porcelain insulators assembled in pairs to accept cables from 3/8 in. thru 4 1/2 in. O.D.
Material	Porcelain

European Specifications (ETIM)

ETIM	EC002470 Mounting clamp for cable protection tubes
Material	Other
Rotatable	N

Packaging

Outer Quantity	10
Outer Dimensions (inches)	12.4x6.4x9.7
Weight Uom	264 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com