



Representative

Catalog Number: N4NY-004B-0-C
Product ID: 7TAG009970R0066
UPC Number: 72849407838
EAN Number: 05414363033967
Status: Active

Plain Edge Cable Clamp, Black Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Width of 9.53mm (0.375 Inches), Thickness of 1.27mm (0.50 Inches), Hole Diameter of 5.2mm (0.203 Inches), #10 Screw Mounting with Closed Diameter of 6.3mm (0.25 Inches)

- Fully radiused inside edges with size markings in inches and millimeters for easy identification.
- Plain edge cable clamps are designed to perform to NAS-1397P.

North American Specifications (UNSPSC)

UNSPSC	39121702 Cable clips
IGCC	5029 Nylon Cable Clips
Brand Name	Catamount
Type	Plain Edge Cable Clamps
Special Features	Fully radiused inside edges with size markings in inches and millimeters for easy identification.
Material	Nylon/Polyamide 6.6
Color	Black
Mounting	#10 Screw

European Specifications (ETIM)

ETIM	EC000127 Saddle
Nominal diameter	6.3mm
Model	Closed
Material	Plastic
Material quality	Polyamide PA

Packaging

Inner Quantity	100
Outer Quantity	10000
Weight Uom	1.25 lbs. per 1000

Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-000389

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com