


# One-way flow control valve GRLA-1/4-QS-8-RS-D

Part number: 534339

★ Core product range

**FESTO**



## Data sheet

Feature	Value
Valve function	One-way flow control function
Pneumatic connection, port 1	QS-8
Pneumatic connection, port 2	G1/4
Adjusting element	Knurled screw
Mounting type	Threaded with external (male) thread
Standard nominal flow rate in flow control direction	475 l/min
Standard nominal flow rate in non-return direction	325 ... 500 l/min
Working pressure	0.2 ... 10 bar
Ambient temperature	-10 ... 60 °C
Assembly position	Any
Operating pressure complete temperature range	0.2 ... 10 bar
Standard flow rate in direction of flow control: 6 -> 0 bar	720 l/min
Standard flow rate in blocked direction: 6 -> 0 bar	610 ... 760 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Storage temperature	-10 ... 40 °C
Medium temperature	-10 ... 60 °C
Maritime classification	see certificate
Nominal tightening torque	5 Nm
Product weight	50 g
Materials note	Conforms to RoHS
Material seals	NBR
Material hollow bolt	Wrought Aluminum alloy Anodized
Material release ring	POM
Material knurled head	Wrought Aluminum alloy Anodized
Material adjusting screw	High alloy steel, non-corrosive
Material swivel fitting	Zinc die-casting