

control cable NEBC-S1G25-K-3.2-N-LE25

Part number: 8001373
☆ Core product range

FESTO



Data sheet

Feature	Value
Electrical connection	25-pin Straight plug/open at one end Sub-D / -
Cable length	3.2 m
Cable diameter	7 mm
Cable structure	Shielded
Protection class	IP40 in assembled condition
Materials note	Contains PWIS substances Conforms to RoHS
Corrosion resistance classification CRC	0 - No corrosion stress
Cable sheath color	Grey
Housing color	Grey