

7-Port USB Charging Station w/Quick Charge 3.0, USB-C Port, Device Storage, 5V 4A (60W) USB Charge Output

MODEL NUMBER: **U280-007-CQC-ST**



Description

Whether you're at home or in the office, Tripp Lite's U280-007-CQC-ST 7-Port USB Charging Station provides enough ports and power to keep your devices at 100% capacity. No more peering behind furniture to find an available outlet or unplugging one device to charge another. You can charge up to seven tablets, smartphones and other devices at the same time. The U280-007-CQC-ST doesn't require a computer, so you can take it anywhere AC power is available.

The U280-007-CQC-ST features five USB-A ports, each capable of delivering up to 5V, 2.4A, which is enough for charging even battery-intensive devices like the Apple® iPad®. A USB-C port provides up to 5V, 3A for more powerful devices. Plus, a Quick Charge 3.0 port is capable of rapid-charging compliant devices up to four times faster than normal USB charging.

In addition, this charging station doubles as a storage unit by providing space to neatly organize cabling while your devices charge. When not in use, cables can be stored in the compartment and kept out of the way. The included adjustable brackets accommodate the number and size of the devices being charged.

To charge your USB devices, simply connect the five-foot power cord's NEMA 1-15P plug to an AC power outlet, and connect your devices to the available USB ports. The unit protects against overheating, overcurrent and overcharging—in fact, it stops charging as soon as your devices' batteries are at full capacity. It also complies with USB Battery Charging (BC) Specification 1.2. The brackets and power supply store conveniently in the charging station when not in use.

Features

Charges Up to 7 Devices at the Same Time

Highlights

- 5 USB-A ports provide up to 5V, 2.4A of charging power
- USB-C port provides up to 5V, 3A of charging power
- Quick Charge 3.0 port charges up to 4x faster than normal charging
- 9 adjustable storage brackets for organizing devices
- Storage compartment neatly organizes your cabling

Package Includes

- U280-007-CQC-ST 7-Port USB Charging Station
- (9) Storage brackets
- External power supply (Input: 100–240V, 50/60 Hz, 1.5A; Output: 15V, 4A)
- C7 to NEMA 1-15P power cord, 5 ft.
- Quick Start Guide



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- Recommended for charging tablets, smartphones and other devices at home or work
- Functions anywhere AC power is available—no computer required

Provides Plenty of Juice for Charging

- Quick Charge 3.0 Class A 5/9/12V technology
- QC 3.0-compliant devices charge up to 4x faster than conventional USB charging
- Delivers up to 5V, 2.4A per USB-A port—enough for charging battery-intensive devices like the Apple iPad
- USB-C port provides up to 5V, 3A of charging power
- Protects against overheating, overcurrent and overcharging
- Complies with USB Battery Charging (BC) Specification 1.2

Efficiently Stores Your Cables / Devices Too

- 9 adjustable brackets provide space to neatly organize devices as they charge
- Convenient storage compartment lets you neatly organize your cabling while your devices charge
- When not in use, cables can be stored in the compartment and kept out of the way

Easy to Use

- External dual-voltage power supply with C8 power inlet and detachable C7 to 1-15P 5 ft. cord
- No computer required

Specifications

MODEL TEXT	
Key Benefit	Charges and organizes up to 7 electronic devices at the same time. Storage compartment neatly organizes your excess cabling to reduce clutter when charging, and stores it out of the way when not in use. Recommended for quick-charging and storing tablets, smartphones and other mobile devices.
OVERVIEW	
AC Adapter	Input: 100-240V, 50/60Hz, 1.5A; Output: 15V, 4A
OUTPUT	
Charging Ports / Amps	(5) 2.4A; (1) 3A / 2A / 1.5A
Charging Method	USB
PHYSICAL	
Unit Dimensions (hwd / in.)	6.6 x 4.9 x 2.6
Unit Dimensions (hwd / cm)	16.8 x 12.5 x 6.6
Unit Weight (lbs.)	1.6



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Unit Weight (kg)	0.73
Color	Black
ENVIRONMENTAL	
Operating Temperature Range	41 to 95 F (5 to 35 C)
Storage Temperature Range	-4 to 122 F (-20 to 50 C)
Relative Humidity	20% to 80%
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>