

USB 3.0 All-in-One Keystone/Panel Mount Extension Cable (M/F), Angled Connector, Black, 1 ft.

MODEL NUMBER: **U324-001-KPA-BK**



Description

The U324-001-KPA-BK USB 3.0 All-in-One Keystone/Panel Mount Extension Cable allows you to terminate a USB 3.0 connection in a universal keystone wallplate or panel. Or you can use the included panel mount adapter to convert the female keystone jack port for installation in a motherboard, podium or kiosk. The angled connector makes the cable easy to install in tight spaces.

Ideal for giving your conference room, classroom, home theater room or retail establishment a professional, tidy look, this one-foot cable can complete an in-wall run and keep components out of sight in a closet or another room to eliminate cable clutter. It supports data transfer rates up to 5 Gbps.

Molded nickel-plated connectors with gold-plated contacts offer optimal signal transfer. Premium foil and braid shielding delivers reliable, error-free signal quality and protection from EMI/RFI interference. Integral strain relief ensures the cable and connectors last a long time. A rugged PVC jacket protects twisted 28 AWG data lines and 24 AWG power lines.

Features

Mounts a USB 3.0 Port in a Fixed Location

- USB-A female keystone jack connector snaps easily into universal keystone wallplate or panel
- Included panel mount adapter allows installation in motherboard, podium or kiosk
- Supports USB 3.0 data transfer rates up to 5 Gbps
- Hides components out of sight to eliminate cable clutter
- Angled female connector for easy installation in tight spaces
- Compatible with all USB-A cables

Highlights

- Connects two USB-A devices, such as computers and flash drives
- Supports USB 3.0 data transfer rates up to 5 Gbps
- Twisted 28/24 data/power lines
- Gold-plated contacts for optimal signal transfer
- Angled female connector for easy installation in tight spaces

Package Includes

- U324-001-KPA-BK USB 3.0 All-in-One Keystone/Panel Mount Extension Cable (M/F), 1 ft.



Premium Construction for Superior Signal Transfer

- Premium foil and braid shielding for error-free signal quality and EMI/RFI protection
- Molded nickel-plated connectors with gold-plated contacts
- Integral strain relief for long life
- Twisted 28/24 AWG data/power lines
- Rugged PVC jacket

Specifications

MODEL TEXT	
Key Benefit	Adds a USB 3.0 female port to a fixed location, such as a universal keystone wallplate, panel, podium or kiosk. Gives your conference room, classroom, home theater room or retail establishment a professional, clutter-free look.
INPUT	
Cable Length (ft.)	1
Cable Length (m)	0.30
PHYSICAL	
Color	Black
CONNECTIONS	
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	USB 3.0 A (FEMALE)
CERTIFICATIONS	
Certifications	RoHS compliant
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>