

USB 3.1 Gen 2 (10 Gbps) Cable, USB Type-C (USB-C) (M/M), 3 ft.

MODEL NUMBER: **U420-003-G2**



Description

The U420-003-G2 USB 3.1 Gen 2 Cable connects and charges two devices with USB-C or Thunderbolt 3 ports or connects a USB-C device to a wall charger with a USB-C port. This three-foot cable supports USB 3.1 Gen 2 data transfer speeds up to 10 Gbps and power output up to 3A for fast charging of mobile devices. Reversible USB-C male connectors plug into a USB port in either direction for fast, fumble-free connection every time.

Premium foil and braid shielding delivers reliable, error-free signal quality and protection from EMI/RFI interference. Molded nickel-plated connectors with gold-plated contacts ensure excellent conductivity. Integral strain relief ensures the cable and connectors last a long time. Backward compatible with previous USB generations.

USB Type-C™ and USB-C™ are trademarks of USB Implementers Forum

Features

Supports USB 3.1 Gen 2

- Connects and charges devices with USB-C ports
- Data transfer speeds up to 10 Gbps—20 times faster than USB 2.0
- Power output up to 3A—perfect for fast charging of most mobile devices
- Backward compatible with previous USB generations

USB-C Male Connectors

- Fumble-free reversible plugs ensure fast, easy connection every time

Highlights

- USB 3.1 Gen 2 data transfer speeds up to 10 Gbps
- Power output up to 3A for fast-charging devices
- Reversible USB-C male connectors on both ends
- Error-free signal quality and EMI/RFI protection
- Compatible with Thunderbolt™ 3 ports

System Requirements

- Devices with a USB-C port

Package Includes

- U420-003-G2 USB 3.1 Gen 2 (10 Gbps) Cable, USB-C (M/M), 3 ft.



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- Compatible with Thunderbolt 3 ports

Premium Construction for Superior Signal Transfer

- Foil and braid shielding for error-free signal quality and EMI/RFI protection
- Molded nickel-plated connectors and gold-plated contacts
- Integral strain relief for long life
- Rugged PVC jacket

Specifications

MODEL TEXT	
Key Benefit	Connects and charges USB-C devices at USB 3.1 Gen 2 speeds up to 10 Gbps.
INPUT	
Cable Length (ft.)	3
Cable Length (m)	0.9
PHYSICAL	
Color	Black
ENVIRONMENTAL	
Operating Temperature Range	14 to 140 F (-10 to 60 C)
Storage Temperature Range	-4 to 185 F (-20 to 85 C)
Relative Humidity	10 to 85%
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>