

Hospital-Grade Computer Power Cord, 15A, 14 AWG (NEMA 5-15P to IEC-320-C13), 25 ft.

MODEL NUMBER: **P006-025-HG15**



Highlights

- Conforms to hospital-grade power cord standards
- Tested to ANSI/UL 62 and 817 and CAN/CSA C22.2 no. 21 and 49
- NEMA 5-15P-HG hospital-grade plug
- 125V/15A rating
- Fully molded ends

Package Includes

- P006-025-HG15 Hospital-Grade Computer Power Cord, 25 ft.

Description

The P006-025-HG15 Hospital-Grade Computer Power Cord features a C13 plug on one end and a NEMA 5-15P-HG plug on the other, allowing you to connect your computer or peripheral to a hospital-grade AC power outlet. It's tested to ANSI/UL 62 and 817, as well as CAN/CSA C22.2 no. 21 and 49 standards, ensuring it's a safe, reliable power solution for hospital environments. The C13 plug connects to computers, printers, scanners, monitors and other electronic devices with a three-pin C14 port. This 25-foot 125V/15A cord features 14 AWG wire, a flexible SJT jacket and fully molded ends for optimum performance.

Features

Safe, Reliable Power Solution for Hospital Environments

- Connects computers and peripherals to a grounded hospital-grade AC outlet
- Ideal for replacing an old or lost cord
- Features C13 female connector and NEMA 5-15P-HG male connector
- Conforms to hospital-grade power cord standards

Optimum Construction

- Tested to ANSI/UL 62 and 817 and CAN/CSA C22.2 no. 21 and 49
- 14 AWG wire
- Flexible SJT jacket
- Fully molded ends
- 125V/15A rating

Specifications



MODEL TEXT	
Key Benefit	Connects your computer or peripheral with a C14 port to any grounded hospital-grade AC power outlet that accepts NEMA 5-15P plugs. Ideal for hospitals and other medical facilities.
INPUT	
Cable Length (ft.)	25
Cable Length (m)	7.6
PHYSICAL	
Color	Black
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	IEC-320-C13
CERTIFICATIONS	
Certifications	ANSI/UL 62 AND 817, CAN/CSA C22.2 NO. 21 AND 49, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>