

Plastic tubing
PUN-H-3/8-BL-150-CB
 Part number: 567950



Data sheet

Feature	Value
Outer diameter, inches	3/8
Bending radius relevant for flow rate	0.171 ft
Min. bending radius	0.081 ft
Tubing characteristics	Suitable for energy chains in applications with high cycle rates
Tubing test conditions	Suitable for energy chains: > 5 million cycles to FN 942021
Temperature dependent working pressure	-14.4 ... 145 Psi
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Food-safe	See Supplementary material information
Ambient temperature	-31 ... 145 °F
Product weight according to length	0.48 oz/ft
Pneumatic connection	For push-in connector outside diameter 3/8"
Color	blue
Shore hardness	D 52 +/-3
Materials note	Free of copper and PTFE Conforms to RoHS
Material tubing	TPE-U(PU)