

Mighty Vue Slim

5-Diopter LED Magnifying Lamp with Brightness Control



- 4.5" x 6", 5-diopter glass lens
- 2.25x magnification
- Distortion-free viewing



- 60 ultra bright SMD LEDs
- LUX rating: 4050LX
- LED lifespan: Min 20,000 hours



- Adjustable tension knob
- Set lamp position and tighten
- Stays in place in any position

Aven's Mighty Vue Slim 5-Diopter LED Magnifying Lamp comes equipped with a 4.5" x 6", 5-diopter crystal clear glass lens for crystal clear, distortion-free viewing at 2.25x magnification. 60 ultra bright SMD LEDs illuminate at 4050LX and for a minumum of 20,000 hours. The sleek lamp head is mounted to a 34" covered spring balanced arm (preventing pinching hazards) with an adjustment knob for secure positioning.

Email | sales@aventools.com



V1_01-2018

MIGHTY VUE SLIM 5 DIOPTER LED MAGNIFYING LAMP			
LUX RATING		4050LX	
LENS		4.5″ x 6″ 5-diopter (2.25x magnification)	
ILLUMINATION		60 SMD LEDs	
POWER ADAPTER		Input: 100-240V AC 50~60Hz, output: 20V 600mA	
POWER CONSUMPTION		1~9W	
ARM		34" covered spring arm	
PACKAGE CONTENTS		Mighty Vue Slim Lamp, heavy duty table clamp, power adapter	
Part #	Description Price		
26505-MX5	Mighty Vue Slim 5-Diopter LED Magnifying Lamp \$145.00		

aventools.com

Phone | 734.973.0099