Xcelite

4" Tapered Head Diagonal Cutter with Green Cushion Grips



Product Details

Catalog No.	MS549J
UPC Code	043127170508
Description	Diagonal
Jaw Type	Flush
Jaw Length	15/32 in.
Head Width	7/16 in.
Head Thickness	9/32 in.
Tip Dimensions	3/64 in.
Packaging	Industrial Box/Carton
Tech. Spec.	MS549J Specifications.pdf
Low Res. I mage	MS549J_100.jpg

Package Details (Dimensions)

MS549J_300.jpg

Normal Stock Item

High Res. I mage

Stock Item

Product Features:

- Tapered head diagonal cutter
- Flush cutting of leads in restricted spaces
- Narrow tips give increased clearance
- Features green cushion grips

Xcelite

4" Tapered Head Diagonal Cutter with Green Cushion Grips




Individual Product								
Catalog No.	MS549J							
UPC Code	043127170508							
Quantity	1							
Length (Inches)	5.6							
Width (Inches)	2.2							
Height (Inches)	0.9							
Gross Weight (lb)	0.2							
Volume (cu in)	11.088							

Catalog No.	MS549J						
I 2 of 5 Code	10043127170505						
Quantity	6						
Length (Inches)	5.66						
Width (Inches)	4.09						
Height (Inches)	1.58						
Gross Weight (lb)	1.2						
Volume (cu in)	36.576						

Catalog No.	MS549J							
I 2 of 5 Code	40043127170506							
Quantity	72							
Length (Inches)	11.65							
Width (Inches)	8.52							
Height (Inches)	5.42							
Gross Weight (lb)	14.4							
Volume (cu in)	537.978							

Tapered Head Diagonal Cutter



- Tapered head diagonal cutter
- Flush cutting of leads in restricted spaces
- Narrow tips give increased clearance
- Features green cushion grips
- Suffix "W" indicates wire catcher

Cat	UPC		Length		A	Α		В		C		E		Pack Wt.	
No.	No.	Packed	Inch	mm	Inch	mm	Inch	mm	Inch	mm	Inch	mm	lb	g	Pack
MS549J	043127170508	Bagged	4	100	15/32	12	7/16	11	9/32	7	3/64	1	.96	435	6
MS549JV	043127085420	Carded	4	100	15/32	12	7/16	11	9/32	7	3/64	1	.96	435	6
MS549JW	043127170539	Bagged	4	100	15/32	12	7/16	11	9/32	7	3/64	1	.96	435	6