

Rittal – The System.

Faster – better – everywhere.

► Enclosure Heaters without fan – SK 3105.340

Date : Mar 19, 2018

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Enclosure Heaters without fan – SK 3105.340

created: 19.03.2018 build on www.rittal.com/us-en



Product description

Supply includes: PTC heater
Quick-connection terminal
Fasteners

Note: For precise temperature control inside the enclosure, we recommend using the enclosure internal thermostat or the digital enclosure internal temperature display and thermostat. In order to prevent condensation on assemblies, hygostat is recommended to regulate heating. In larger enclosures, even heat distribution is best achieved by installing several low-output heaters. The installation of heaters is generally advisable, in order to prevent condensation.

Note on Model No.: Special voltages available on request. We reserve the right to make technical modifications.

Product features

Continuous thermal output at 10°C: 49 W - 50 W

Rated operating voltage: 110 V - 240 V, 1~, 50 Hz/60 Hz

Dimensions: Height: 155 mm (6.1 ")
Width: 64 mm (2.5 ")
Depth: 56 mm (2.2 ")

Miniature circuit-breaker/fuse: 4 A

Packaging unit: 1 pc(s).

Weight/packaging unit: 0.4 kg (0.9 lb.)

EAN:	4028177638648
Customs tariff number:	85162999
ETIM 6.0:	EC000737
ETIM 5.0:	EC000737
eCl@ss 8.0/8.1:	27180710
eCl@ss 7.0/7.1:	27180710
eCl@ss 6.0/6.1:	27180710
eCl@ss 5.1/5.1.4:	27180710
Product description (long):	SK enclosure heater, without fan, 49-50 W, 110-240 V, 1~, 50/60 Hz, WHD: 64 x 155 x 56 mm
Approvals	
Approvals:	Approval overview CSA UR + C-UR VDE
Certificates:	EAC
Declarations:	Declaration of conformity