Rittal - The System.

Faster – better – everywhere.

TS System Chassis 17 x 73 mm – TS 8612.080

Date: Mar 19, 2018



TS System Chassis 17 x 73 mm – TS 8612.080 created: 19.03.2018 build on www.rittal.com/us-en



Product description	
Version:	For the inner mounting level and for mounting on doors
Description:	Variable, with 5 rows of holes for universal skeleton structures or partial assembly. Simply position in the TS holes and secure.
Material:	Carbon steel
Surface finish:	Zinc-plated
Mounting tip:	The rail for interior installation is required when installing in CM, TP
Supply includes:	Assembly screws
Product features	
Suitable for:	Width/depth: 800 mm
Dimensions:	Length: 790 mm (31 ")
Installation options:	On the vertical TS enclosure profile: on the outer mounting level, all-round, height-offset For SE, may additionally be mounted on the top horizontal section in the depth In the tubular door frame for TS, SE and PC In CM and TP via rails for interior installation: in width, for inner mounting level Simply locate installation kit into component shelves and secure. One pack is sufficient for 2 component shelves. 100 kg surface load, static
Suitable for door width:	900 mm

© Rittal 2018

Packaging unit:	4 pc(s).
Weight/packaging unit:	3.58 kg (7.9 lb.)
EAN:	4028177212107
Customs tariff number:	73269098
ETIM 6.0:	EC002625
ETIM 5.0:	EC002625
eCl@ss 8.0/8.1:	27189234
eCl@ss 7.0/7.1:	23159101
eCl@ss 6.0/6.1:	23159101
eCl@ss 5.1/5.1.4:	27189250
Product description (long):	TS TS punched section with mounting flange, 17 x 73 mm, for inner mounting level: for W/D: 800 mm, for door width: 900 mm, L: 790 mm
Approvals	
Certificates:	EAC

© Rittal 2018