

Rittal – The System.

Faster – better – everywhere.

▶ TS System Chassis 17 x 73 mm – TS 8612.150

Date : Mar 19, 2018

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS System Chassis 17 x 73 mm – TS 8612.150

created: 19.03.2018 build on www.rittal.com/us-en



Product description

Version:	For the outer mounting level
Description:	Variable, with 5 rows of holes for universal skeleton structures or partial assembly. Simply position in the TS holes and secure.
Material:	Carbon steel
Surface finish:	Zinc-plated
Mounting tip:	The rail for interior installation is required when installing in CM, TP
Supply includes:	Assembly screws

Product features

Suitable for:	Width/depth: 500 mm
Dimensions:	Length: 440 mm (17 ")
Installation options:	On the vertical TS enclosure profile: on the outer mounting level, all-round, at the same height For SE, may additionally be mounted on the top horizontal section in the depth In CM and TP via rails for interior installation: in depth, for outer mounting level
Packaging unit:	4 pc(s).
Weight/packaging unit:	1.99 kg (4.4 lb.)

EAN: 4028177212145

Customs tariff number: 73269098

ETIM 6.0: EC002625

ETIM 5.0: EC002625

eCl@ss 8.0/8.1: 27189234

eCl@ss 7.0/7.1: 23159101

eCl@ss 6.0/6.1: 23159101

eCl@ss 5.1/5.1.4: 27189250

Product description (long): TS TS punched section with mounting flange, 17 x 73 mm, for outer mounting level: W/D: 500 mm, L: 440 mm

Approvals

Certificates: EAC