

ENGLISH

Datasheet

RS Pro CMJ Common Mode Choke, $0 \rightarrow +70$ °C, 7.6 x 5.8 x 4.3mm

RS Stock No: 104-8400



Product Details

RS Pro common mode choke measures 7.6 x 5.8 x 4.3 mm. This miniature SMD choke is ideal for pick-and-place compatibility. The common mode choke comes with various inductance values and offers high attenuation over a wide frequency range.

Features and Benefits

- Ratings at 25°C ambient
- Operating temperature range: 0 to 70°C
- Pick and place compatibility



ENGLISH

Specifications:

Mounting Type	Surface Mount
DC Resistance	250 mΩ
Depth	5.8 mm
Dimensions	7.6 x 5.8 x 4.3 mm
Height	4.3 mm
Length	7.6 mm
Maximum Operating Temperature	+70°C
Minimum Operating Temperature	0°C
Maximum Current	500 mA
Operating Temperature Range	0 to +70°C
Inductance	1000 µH
Number of Lines	2