

Datasheet

RS Pro Mini USB-A Series, Type A USB Connector, Panel Mount Plug, GT111200

RS Stock No: 111-6749



Product Details

RS Pro mini USB A Series panel mount connector has a superior quality waterproof housing construction for added protection and durability. This IP65/IP67 rated connector is manufactured from rugged thermoplastic materials making them suitable for harsh environment, where the protection from water and dust ingress is essential.

Features and Benefits

- IP65/IP67 rated
- Rugged construction
- RoHS compliant
- Suitable for harsh environments

Specifications:

Contact Material	Copper Alloy
Current Rating	1.5 A
Gender	Male
Maximum Operating Temperature	+105°C
Minimum Operating Temperature	-40°C
Mounting Type	Panel Mount
Number of Ports	4
Colour	Black
Contact Resistance	30 mΩ
Dimensions	32.9 x 28.6 x 19 mm
Housing Material	Thermoplastic
Insulation Resistance	1000 MΩ
IP Rating	IP67
Wire Size	22 to 28 AWG