

Datasheet

RS Pro Multi Function 33 Time Delay Relay, PCB Pin, 01.s

→ 999 days, 2 Contacts, 110 → 240 V ac

RS Stock No: 896-6872



Product Details

RS Pro multi function 33 time delay relay has up to 33 standard timing functions and is easily programmable. You can also configure the time delay relay to a custom timing that suits your requirements perfectly. It has a terminal type PCB pin and has a time range of 01. s to 999 days. It has 2 contacts and supply voltage of 110 to 240 V ac.

Features and Benefits

- 2 x 4-digit 7 segment display
- Panel/flush mounting (896-6872), DIN/base/socket mounting (896-6879)
- 33 default modes
- Wide range of applications and multiple operating modes
- User friendly keys and key operations with lock and unlock facility
- High timing accuracy
- 0.1 s to 999 days timing range
- Wide signal sensing range
- Wide supply voltage range
- IP30 protection

**Specifications:**

Number of Timer Functions	Multi Function
Power Supply	External
Switch Configuration	DPDT
Time Increment	Days, Hours, Minutes, Seconds
Depth	92.5 mm
Length	48 mm
Maximum Operating Temperature	+55°C
Minimum Operating Temperature	-5°C
Number of Contacts	2
Width	48 mm
Contact Configuration	2CO
Current Maximum	5 A
Current Minimum	2 A
Maximum Voltage	240 V ac
Minimum Voltage	110 V ac
Mode of Operation	Multi Function
Mounting Type	Panel Mount
Supply Voltage	110 to 240 V ac
Terminal Type	PCB Pin
Time Delay	200 ms
Time Range	0.1 s to 999 days
IP Rating	IP20, IP40