

ENGLISH

Datasheet

RS Pro Hours Run Meter, 6 digits, Digital, Spade Terminal Connection, 90 \rightarrow 264 V ac RS Stock No: 896-6933



Product Details

RS Pro hours run meter has a robust design that enables a high degree of accuracy and it has 50.8 cut-out size. The design of this round meter makes it totally sealed from dust and moisture. It has 6 digits with digital spade terminal connection and has a supply voltage of 90 to 264 V ac.

Features and Benefits

- 7 different bezel style models
- Panel mount
- 6 digits non-resettable with automatic recycle to zero
- Compact and robust design provides shock and vibration protection
- Wide supply voltage range
- IP66 protection



ENGLISH

Specifications:

Approvals	CE; cRUus; NEMA 4X; RoHS Compliant; SAE
Count Direction	Up
Function	Hour Meter
Meter Type	Electronic
Shape	Round
Cutout Height	24.1 mm
Depth	70.5 mm
Maximum Count Frequency	50/60 Hz
Maximum Measurement	99999.9 h
Measurement Range	0 to 99999.9 h
Meter Accuracy	±0.02%
Minimum Measurement	0 h
Minimum Operating Temperature	-40°C
Number of Digits	6
Weight	47 g
Connection Type	Spade
Count Capacity	99999.9 h
Cutout Size	50.8 (dia.) mm
Digit Height	3.6 mm
Display Type	Digital
Input Type	Voltage
Mounting Type	Panel Mount
Reset Method	No Reset
Supply Voltage	90 to 264 V ac
Humidity Rating	95%
IP Rating	IP65
Power Rating	0.5 VA

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.