

Datasheet

RS Pro Hours Run Meter, 6 digits, Digital, Spade Terminal Connection, 270 → 460 V ac, 90 → 264 V ac

RS Stock No: **896-6945**



Product Details

RS Pro hours run meter has a robust design that enables a high degree of accuracy and it is compact in size. The design of this rectangular meter makes it totally sealed from dust and moisture. It has 6 digit display with digital spade terminal connection and has a supply voltage of 270 to 460 V ac and 90 to 264 V ac.

Features and Benefits

- 7 different bezel style models
- Panel mount
- 6 digits non-resettable with automatic recycle to zero
- Compact and robust design provides shock and vibration protection
- Wide supply voltage range
- IP66 protection

Specifications:

Approvals	CE; RoHS Compliant
Count Direction	Up
Function	Hour Meter
Meter Type	Electronic
Shape	Rectangular
Cutout Height	100 mm
Cutout Width	45 mm
Depth	45 mm
Maximum Count Frequency	50/60 Hz
Maximum Measurement	99999.9 h
Measurement Range	0 to 99999.9 h
Meter Accuracy	±0.02%
Minimum Measurement	0 h
Minimum Operating Temperature	-5°C
Number of Digits	6
Weight	70 g
Connection Type	Spade
Count Capacity	99999.9 h
Cutout Size	100 x 45 x 36 mm
Digit Height	3.6 mm
Display Type	Digital
Input Type	Voltage
Mounting Type	DIN Rail
Reset Method	No Reset
Supply Voltage	270 to 460, 90 to 264 V ac
Humidity Rating	95%
IP Rating	IP20, IP40
Power Rating	1 VA