

ENGLISH

Datasheet

RS Pro Hours Run Meter, 6 digits, LCD, Screw Connection, $85 \rightarrow 265$ V ac RS Stock No: 896-6951



Product Details

RS Pro hours run meter comes in a small variety of bezels and a wide range of supply voltage. This digital round meter has 6 digit LCD display with remote reset feature. It has a supply voltage of 85 to 265 V ac.

Features and Benefits

- 6-digit (5 mm) LCD display
- Panel mount
- Wide range of supply voltage
- Remote reset
- Available in 3 different bezels (depending on model)
- Lower power consumption



Power Rating

ENGLISH

Specifications: Approvals RoHS Compliant; CE; UL94 V-0 Up Count Direction Function Hour Meter Electronic Meter Type Shape Round **Cutout Height** 24.6 mm **Cutout Width** 37 mm 42.5 mm Depth Maximum Count Frequency 50/60 Hz Maximum Measurement 99999.9 h +50°C Maximum Operating Temperature 0 to 99999.9 h Measurement Range $\pm 0.02\%$ Meter Accuracy Minimum Measurement 0 h Minimum Operating Temperature -10°C Number of Digits 6 35 g Weight **Connection Type** Screw **Count Capacity** 99999.9 h Cutout Size 37 x 24.6 mm Digit Height 5 mm **Display Type** LCD Input Type Voltage Mounting Type Flush/Panel Mount **Reset Method** Remote Supply Voltage 85 to 265 V ac Humidity Rating 95% IP54 **IP** Rating

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.

0.8 VA