



ENGLISH

Datasheet

RS Pro USB A Power Adaptor Global Plug

RS Stock No: 899-8592



Features:

- Universal / Full Range Input
- Interchangeable AC Heads
- Level 6 Efficiency
- Cost Effective & Highly Reliable



Specifications:

Output Voltage	5V
Output Current Max.	2A
Output Current Min.	0A
Power (Watts)	10W
Output Regulation	+/-5%
Ripple & Noise (mV p-p)	300 (mV p-p)
Protections	Over Current Short Circuit Over Current
Rated Input Voltage	100 – 240V ac
Full Input Voltage Range	90 – 264V ac
Rated Frequency	50/60Hz
Full Frequency Range	47/63Hz
Efficiency	79%
Input Current (RMS Max.)	0.3A
Inrush Current	No Damage
Turn on Delay	3 Seconds Max.
AC Inlet	Interchangeable UK, Euro, US & Aus Plugtop
DC Outlet	5V dc USB Outlet
Operating Temperature	0 to 40°C
Storage Temperature	-20 to 60°C
Operating Humidity	20 – 85%
Storage Humidity	5 – 95%
Safety Approvals	CE, C-Tick, CCC, cULus, TUV gs
PB-Free	Yes RoHS Compliant
Dimensions (mm)	60.9 x 31.4 x 38