

## Datasheet

# RS Pro Analogue Panel Ammeter 20A AC, 68mm x 68mm Moving Iron

RS Stock No: **901-0346**



## Product Details

RS Pro analogue panel ammeter has cut-out dimensions of 68 x 68 mm, is a moving iron for 20 A ac current. It has ABS and polycarbonate enclosure. The operating temperature ranges from -25 to +50°C.

## Features and Benefits

- Panel mounting
- Case and terminal protection material UL 94VO
- 1.5 accuracy class
- IEC51, BS89, DIN 43780, VDE 0410 standard

**Specifications:**

Approvals	RoHS Compliant; CE; TUV; UL E327849; IEC 51; BS 89; DIN 43780; VDE 0410
Current Type	AC
Meter Type	Moving Iron
Moving Element	Moving Iron
Cutout Height	68 mm
Cutout Width	68 mm
Depth	36.5 mm
Maximum Temperature	+50°C
Maximum Value	20 A
Measurement Range	0 to 20 A
Minimum Displayed Value	0 A
Minimum Temperature	-25°C
Meter Accuracy	±1.5%
Dimensions	72 x 72 mm
Enclosure Material	ABS, PC
Mounting Type	Panel Mount