

Datasheet

RS Pro AC Analogue Panel Voltmeter, 500V, 46 x 46 mm,

RS Stock No: **901-0523**



Product Details

RS Pro analogue panel voltmeter has cut-out dimensions of 46 x 46 mm, is a moving iron for 500 V ac current. It has ABS and polycarbonate enclosure. The operating temperature ranges from -25 to +50°C.

Features and Benefits

- Panel mounting
- Case and terminal protection material UL 94V0
- 1.5 accuracy class

**Specifications:**

| | |
|-------------------------|-------------------------------------|
| Approvals | RoHS Compliant; CE; TUV; UL E327849 |
| Current Type | AC |
| Meter Type | Moving Iron |
| Cutout Height | 46 mm |
| Cutout Width | 46 mm |
| Depth | 39 mm |
| Maximum Displayed Value | 500 V |
| Maximum Temperature | +50°C |
| Measurement Range | 0 to 500 V |
| Minimum Displayed Value | 0 V |
| Minimum Temperature | -25°C |
| Cutout Size | 46 x 46 mm |
| Meter Accuracy | 1.5% |
| Dimensions | 48 x 48 mm |
| Enclosure Material | ABS, PC |
| Mounting Type | Panel Mount |
| | |