

### ENGLISH

## Datasheet **RS Pro DC Analogue Panel Voltmeter, 40V, 92 x 92 mm,** RS Stock No: **901-0567**



#### **Product Details**

RS Pro analogue panel voltmeter has cut-out dimensions of 92 x 92 mm, is a moving iron for 40 V dc current. It has ABS and polycarbonate enclosure. The operating temperature ranges from -25 to +50°C.

#### **Features and Benefits**

- Panel mounting
- Case and terminal protection material UL 94VO
- 1.5 accuracy class



# ENGLISH

### **Specifications:**

Approvals	RoHS Compliant; CE; TUV; UL E327849
Current Type	DC
Meter Type	Moving Coil
Cutout Height	92 mm
Cutout Width	92 mm
Depth	45 mm
Maximum Displayed Value	40 V
Maximum Temperature	+50°C
Measurement Range	0 to 40 V
Minimum Displayed Value	0 V
Minimum Temperature	-25°C
Cutout Size	92 x 92 mm
Meter Accuracy	±1.5%
Dimensions	96 x 96 mm
Enclosure Material	ABS, PC
Mounting Type	Panel Mount