



ENGLISH

Datasheet

# LED 3AAA 400LM High Power Focusing Torch

RS Stock No: 901-4972





ENGLISH

### **Sizes:**

Torch Overall Length (mm): 128

Diameter (Ø mm): Head - Ø 35, Barrel – Ø 28.5

Batteries Inserted: 3 X AAA

Batteries Supply: Not Included

Weight (gm), Torch Only: 121

### **Materials/Parts:**

Case: 6463 Aluminium Alloy

Lens: PC

LED: CREE X-PL V4

Package: Folded PVC Blister with RS Card Inserted

### **Features:**

Depressing Tail Cap Switch

**Switching Modes – High ON/Low ON/Flash ON/OFF**

Functioned by 3 X AAA Batteries

Carrying Holster Included

**Slide Focus from Flood to Spot**

**Built-in Multi Option Battery Holder in Use – 3 X AAA, 2 X AAA or 1 X AAA**

Lumen Output (**ANSI FL1 STANDARD**):

3 X AAA – 400 LM at High, 150 LM at Low

2 X AAA – 200 LM at High, 70 LM at Low

1 X AAA – 100 LM at High, 30 LM at Low



**ENGLISH**

**Battery Run Time (100% to 10%, ANSI FL1 STANDARD):**

**3 X AAA – 5 Hrs at High, 15 Hrs at Low**

**2 X AAA – 3.5 Hrs at High, 10.5 Hrs at Low**

**1 X AAA – 2.5 Hrs at High, 7.5 Hrs at Low**

**Battery Power Indicator:** On Grip, the indicator turned from GREEN to RED when power is less than 20%

**Water Resistant:** IPX6

**Drop Impact Test:** 1 Meter

**Taiwan and USA Patented**

**Colour:**

Metal Pewter Anodized Colour

**Marking:**

RS Laser Engraved Logo on Torch

07/01/2016 Version No. 001