



ENGLISH

Datasheet

RS Pro WiFi Snake Scope

RS Stock 913-1566

RS Pro WiFi Snake Scope is a unique device that can wirelessly stream high-quality videos from a camera-head to the screen of your Smartphone or Tablet. This device is designed to inspect hard to reach or hard to see areas.



Technical Information

- Supported Platform: IOS Platform (iPhone3GS /iPhone4 /iPhone4S / iPad /iPad2)

RF:

- WiFi 802.11n Specification.
- Transmission distance: 50 m (Line of sight).

Security:

- Support WEP encryption
- User Name and Password required to connect to the Wireless camera

Video Codec:

- MPEG4/M-JPEG compression and decompression.
- IOS Platforms only support MPEG4 video format

Technical Specification

Wireless between monitor and handle	YES, WiFi not 2.4G, Not Bluetooth
Probe waterproof	YES IP67 (1 meter 30 minutes)
Support Video Recording	YES
CAMERA SENSOR Resolution	640 x 480 Pixels
White comparison	automatic
Exposure to light	automatic
Camera illumination	4 LEDs, white
Power Supply	4 x 1.5V AA
Operating temperature	0 to+45°C
Operating Humidity	15 - 85% RH
Storage temperature	.-10 to +50°C
Storage Humidity	15 - 85% RH
Metal tube length	88.0 +- 2.0 cm
Minimum Bending radius	4.5 cm
Diameter of camera head	8.0 mm
Lens coverage	54°
Focus	> 3 cm
Weight without accessories	Approx. 270 g

Application Information

The RS Pro WiFi Snake Scope is ideal for inspecting crowded engine compartments, equipment enclosures or HVAC ductwork.