



**Datasheet**  
**Stock No: 913-2103**

**ENGLISH**

## **4-Way, 5-Pole Nylon Screw Terminal Block**



### **Description**

The practical, easy and safe way to connect 2, 3 or 4 wires together, each with its own screw clamp.

Each of the 5 segments is a single pole.

Supplied as a 5 segment block which can be cut to size.

### **Technical Data**

- Dimensions: L100mm x W40mm x H130mm
- Weight: 20 g (approx.); each segment is 4 g
- Rated insulation voltage: 450 V
- Rated current: 24 A
- Rated connecting capacity: min. 1.0 mm<sup>2</sup>; max. 2.5 mm<sup>2</sup>
- Number of poles: 5, and can be cut into individual poles
- Maximum ambient operating temperature: +40 °C
- Accepts flexible and solid conductors

### **Approvals**

- VDE Testing and Certification Institute GmbH Certificate No. 40041927
- Conforms with the European Directive 2006/95/EC

