

Datasheet

Stock No: 9175096**RS Pro Oil Resistant Delivery Hose**

Internal Diameter	51.6mm
	2"
External Diameter	60.9mm
Wall Thickness	4.7mm
Maximum Working Pressure	7.3 Bar
Weight Per Meter	1.04 Kg
Bend Radius	230mm
Vacuum Mtrs H2O	9
Material	Flexible PVC
Working Temperature	-10°C to +55°C
Length	10 M