

Datasheet

**Stock No: 9175106****RS Pro Oil Resistant Delivery Hose**

Internal Diameter	25.4mm
	1"
External Diameter	33.8mm
Wall Thickness	4.2mm
Maximum Working Pressure	9.3 Bar
Weight Per Meter	0.49 Kg
Bend Radius	113mm
Vacuum Mtrs H2O	9
Material	Flexible PVC
Working Temperature	-10°C to +55°C
Length	5 M