


Patch cable - FL CAT5 PATCH 5,0 - 2832580

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Patch cable, CAT5, assembled, 5 m



Key Commercial Data

Packing unit	10 STK
GTIN	 4 046356 044080
GTIN	4046356044080

Technical data

Ambient conditions

Ambient temperature (operation)	-10 °C ... 60 °C
---------------------------------	------------------

External sheath

Outer sheath, material	LSFROH
External diameter	5.50 mm
External diameter max.	6.2 mm

Single wire

Single wires, quantity	8
Single wire, material	Cu litz wire
Single wire, cross section	0.14 mm ²

Mechanical properties

Smallest bending radius, fixed installation	30 mm
---	-------

General

Conductor length	5 m
Nominal voltage U _N	150 V _{rms}
Transmission characteristics (category)	CAT5

Patch cable - FL CAT5 PATCH 5,0 - 2832580

Technical data

Behavior in fire

Flame resistance	according to IEC 60332-3C
Concentration of fumes	in accordance with IEC 61034
Halogen-free	according to IEC 60754-1

Standards and Regulations

Concentration of fumes	in accordance with IEC 61034
Flame resistance	according to IEC 60332-3C
Halogen-free	according to IEC 60754-1

Approvals

Approvals

Approvals

EAC / DNV GL

Ex Approvals

Approval details

EAC		B.01742
-----	---	---------

DNV GL	http://exchange.dnv.com/tari/	TAE000020G
--------	---	------------

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>