

Crimping pliers - CRIMPFOX CENTRUS 10H - 1213156

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Crimping pliers, for uninsulated and insulated ferrules, DIN 46228 Part 1 and 4, from 0.14 mm² ... 10 mm², also for TWIN ferrules up to 2 x 4 mm², automatic cross section adjustment, lateral insertion, equipped with fall protection

Why buy this product

- ✓ Ergonomic handle design ensures comfortable, fatigue-free handling
- ✓ With a particularly small handle width, the tool fits perfectly in your hand
- ✓ Sturdy plastic guard over the head of the pliers protects the tool against damage caused by dropping
- ✓ Up to 30% lower actuation force, thanks to optimized leverage
- ✓ Pressure lock ensures consistently high quality crimping results



Key Commercial Data

Packing unit	1 STK
GTIN	 4 055626 212630
GTIN	4055626212630

Technical data

Dimensions

Length (b)	180 mm
Width (a)	70 mm

General

Color	black
Compression	HEX crimp
Type of contact	Insulated and uninsulated ferrules
Designation	Crimping position 1
Min. cross section	0.14 mm ²
Max. cross section	10 mm ²
AWG min	26

Crimping pliers - CRIMPFOX CENTRUS 10H - 1213156

Technical data

General

AWG max	8
Weight	380 g
Min. cross section	0.14 mm ²
Max. cross section	10 mm ²

Approvals


Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU x- DE.xx08.B.02974
-----	---	--------------------------

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>