

Thermomagnetic device circuit breaker - TMCP 1 M1 300 10,0A - 0915836


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Thermomagnetic circuit breaker, 1-pos., normal blow, 1 N/O contact and 1 N/C contact



Key Commercial Data

Packing unit	6 STK
GTIN	 4 017918 600679
GTIN	4017918600679
Sales Key	04

Technical data

General

Mounting type	on base element
Color	black
Number of positions	1
Overvoltage category_GRP	II
Insulating material	PA66
Flammability rating according to UL 94	V-2

Electrical data

Fuse type	Automatic device
Rated surge voltage	2.5 kV
Rated voltage	250 V AC 65 V DC
Rated current I _N	10 A
Insulation resistance R _{iso}	> 100 MΩ (500 V DC)
Rated short-circuit switching capacity I _{cn}	800 A 2500 A (32 V DC)

Thermomagnetic device circuit breaker - TMCP 1 M1 300 10,0A - 0915836

Technical data

Electrical data

Short-circuit switching capacity I_k	5000 A (UL 1077: 277 V AC)
	2000 A (UL 1077: 65 V DC)
Dielectric strength	3000 V AC (Actuation area)
	1500 V AC (Main to auxiliary circuit)
	1000 V AC (Auxiliary circuit 11 - 12 to 23 - 24)
Switching cycles, max.	10000 (At $1 \times I_n$, inductive)
Degree of pollution	2
Overvoltage category_GRP	II
Insulating material group	II

Dimensions

Height	50 mm
Width	12.5 mm
Depth	78.5 mm
Complete module height	115 mm
Complete module width	38 mm
Complete module depth	121 mm

Ambient conditions

Degree of protection	IP30 (Actuation area)
	IP00 (Connection area)
Ambient temperature (operation)	-30 °C ... 60 °C

Connection data

Connection method	pluggable
-------------------	-----------

Standards and Regulations

Standards/specifications	EN 60934
	UL 1077

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Approvals

Approvals

Approvals





CSA / UL Recognized / EAC / VDE Zeichengenehmigung

Ex Approvals

Thermomagnetic device circuit breaker - TMCP 1 M1 300 10,0A - 0915836

Approvals

Approval details

CSA		http://www.csagroup.org/services-industries/product-listing/	074317
UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 140459
EAC			RU C- DE.A*30.B01546
VDE Zeichengenehmigung		http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx	40029348

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>